

The CHT and SpectraTrend HT are based on different communication protocols and therefore the cabling is NOT interchangeable.

New cabling is provided with the SpectraTrend HT including a 30 meter Sensor and Power DIO cable (L02-1014-766) for connecting the sensor to the support box, and 20 meters of Ethernet cable (L02-1014-767) for connection from a PC running EasyMatch ST software to the sensor head.

The only cabling that can be reused is the analog cable, if both systems are equipped with this option. The analog cable is 4 twisted pairs and connect between the support unit and the customers PLC (DCS).