

**D02-1014-367 45/0 LAV Nose Cone with Screw-On Glass Port**

Provides a user-installable, modified nose cone base with a replaceable A02-1014-374 screw-on end cap with glass port. This port is designed to protect the instrument from dust, fluff and moisture.

Includes a replaceable A02-1014-435 screw-on end cap with a 32 mm open port to run instrument diagnostics.

This modified nose cone can be installed on MSEZ/MSXP/MSXE 45/0 LAV sensors.

**A02-1014-374 MSEZ 45/0 LAV Replacement Screw-On Glass End Cap**

Replacement screw-on end cap with glass port for D02-1014-367 MSEZ Nose Cone that can be user-installed in the field.